

Fiery® PC21

Fiery FS700 Pro



Redefining the future of color and production automation

Powering the Revoria Press PC2120, the Fiery PC21 delivers advanced color accuracy beyond traditional limits, combining exceptional processing performance with professional workflow and color tools, including Fiery JobExpert™ and the Fiery Graphic Arts Pro Package.

Maximize throughput with intelligent performance

The Fiery PC21 includes Intelligent Fiery HyperRIP™ for high-speed processing of complex production jobs. It automatically maximizes throughput and reduces bottlenecks, while Fiery JobExpert™ optimizes job settings to reduce manual preparation and accelerate production.

Expand color possibilities with unprecedented accuracy

- Extend the achievable color space through pink and green gamut expansions, delivering added vibrancy, smoother transitions, and brighter highlights.
- Protect brand integrity with the highest precision in spot color reproduction, even for challenging colors.
- Gain greater confidence in color quality with Fiery ImageViewer for visual color refinement and Fiery Spot Pro for advanced spot color control.

Automate color management

Simplify color setup and maintain long-term consistency using 1-step color management and Zero-touch recalibration, helping deliver accurate, repeatable results with minimal operator intervention, including CMYK+ workflows.





Fiery® PC21 specifications

Fiery Driven™ engines

- Revoria Press™ PC2100
- Supports all engine finishing devices

Hardware and platform

- Intel Xeon Dual 12 Core processor
- 32 GB RAM
- SSD boot drive for OS & Fiery software + 2 x 2 TB HDD
- USB 3.0: 4 rear ports, 3 on QuickTouch™ panel
- Calibration: Inline sensor or ES-3000 spectrophotometer
- Fiery FS700 Pro system software
- Windows 10 IoT Enterprise 2021 LTSC
- Fiery Installer Builder

Productivity and workflow

- Fiery Command WorkStation®
- Fiery JobExpert™
- Fiery Intelligent HyperRIP
- Fiery JobFlow™ Base
- Fiery Smart Estimator
- Fiery Print Scheduler
- Print Time Estimation
- Fiery Impose**
- Fiery JobMaster**
- Fiery Hot Folders/Virtual Printers
- Fiery drivers for Linux, Windows and Mac®
- Fiery WebTools™
- Fiery server presets
- Fiery Go (Android™ and iOS)
- Fiery Paper Catalog
- Spool-RIP-Print simultaneously
- Rush Printing, Suspend on Mismatch, Job Reorder, Proof Print
- Strict ordered printing
- Sample Print
- Pad printing
- Auto trapping
- Slip sheet, job cover page and offset by sheets, copies or sets
- Fiery Custom Crease
- Fiery IQ: Dashboard, Insight, Notify, Fiery IQ Go

Color and imaging

- Fiery Edge™ color profiles
- Fiery Edge spot color processing
- CMYK+ Capabilities
 - Gamut extension (Pink, Green)
 - Specialty colors (Gold, silver, white, clear, textured paper)
 - Supports all engine specialty toners
 - Fiery Spot Pro enables creation of dazzling custom spot colors
 - Multi-Pass Printing for tactile, dimensional effects
 - Invert specialty color
 - Double print specialty color
- 1-step color management
- Zero-touch recalibration
- Fiery Color Profiler Suite with ES-3000 spectrophotometer
- PANTONE® Color Enabled
- Object Oriented Halftones
- RGB and CMYK rendering intent control
- Fiery Ultra Smooth Gradients (1200 x 1200 dpi, 10-bit rendering resolution)
- Text and graphics enhancement
- Fiery Graphic Arts Pro Package**
 - Fiery Spot Pro, Fiery ImageViewer, Fiery Preflight Pro, Fiery Postflight, Fiery Control Bar Builder
- Composite overprint
- Cutback trapping
- Image smoothing
- Fiery Image Enhance Visual Editor
- Fiery TrueBrand

Variable data printing

- Fiery FreeForm™ Create
- Supported file formats:
 - Fiery FreeForm Plus, PPML v2.x/3.0, PDF/VT 1 and 2, Creo VPS
- VDP Record and Set Level Finishing, VDP Record Range Printing, Define Record Length, VDP Raster Preview, VDP imposition

Adobe interpreter support

- Adobe® PDF Print Engine® 6.2***
- CPSI version 3020

File format support

- Adobe® PostScript® Levels 1, 2, 3; Adobe PDF; PDF/X-1a, 3, and 4; EPS; JPEG; TIFF
- Microsoft Office document formats: doc, docx, xls, xlsx, ppt, pptx, pub (via Hot Folders)

Security

- Secure Erase (NIST 800-88 compliant), Security profiles
- FIPS 140-2 compliant data encryption
- ISO/IEC 15408 & IEEE Std 2600 (Common Criteria) compliant****
- Port blocking, IP filtering, 802.1x advanced authentication methods, Secure connections using HTTPS with support for TLS 1.3, (NIST 800-52 Compliant) IPsec network encryption
- Secure Printing, USB security, Port-based access controls
- Digitally signed software updates
- Windows 10 OS security features
- Authentication/Accounting

Networking/Connectivity

- TCP/IP, AppleTalk, Bonjour support, SNMP, Port 9100, IPP 2.0, FTP, SMB, WSD, point and print, print via email (PS/PDF), IPv6 support, LDAP authentication
- Login with SSO (single sign-on)
- Native support for Universal Print by Microsoft®
- Compliant with Mopria® industry standard

EMC

- FCC Title 47, Part 15 Subpart B, ISED of Canada, ICES-003, EN55032: 2015 +A11:2020, EN 55035: 2017/A11:2020, AS/NZS CISPR 32: 2013, CCC-China, KC-Korea, BSMI-Taiwan

Safety

- CB Scheme-IEC-62368-1, 2nd Edition, EN 62368-1, 2nd Edition, CE Mark (EU), cTUVus -NA, CCC-China, BSMI-Taiwan

Integration

- JDF v1.8
- Fiery API
- MIS and Web-to-Print integration ready
- Prepress workflow integration (FUJIFILM XMF Workflow, Agfa® Apogee, Kodak® PRINERGY, Heidelberg® Prinect, SCREEN EQUIOS)

Optional Fiery software and hardware

- Fiery Dual Specialty Toner Package
- Fiery IPDS
- Fiery ColorGuard*
- Fiery Compose*
- Fiery JobFlow*
- Fiery JobFlow Pro*
- Fiery High Security Kit V1.0
- Fiery NX Station (LS / GL)
- Fiery Manage
- Fiery disk drive security kits

Power

- Auto-switching: 100–240 VAC
- 50/60 Hz, 6 Amps @100 VAC, 5 Amps @240 VAC
- Maximum power usage: 600 W
- Typical power usage: 200 W

Dimensions/Weight

- Height: 20.75" (527.05 mm), Width: 9.25" (234.95 mm), Depth: 22.5" (463.55 mm)
- Weight: 48 lbs (21.77 kg)

* Free 30-day trial available
 ** Includes 5-year term license
 *** Updated with enhancements and service releases on an ongoing basis
 **** With proper configuration by end customer or service provider

FUJIFILM Corporation
 Authorized Distributor

global.fujifilm.com

The product specifications, appearance and other details in this brochure are subject to change without notice for improvements.

Trademarks • FUJIFILM and FUJIFILM logo are registered trademarks or trademarks of FUJIFILM Corporation. • Revoria, Revoria logo and Revoria Press are registered trademarks or trademarks of FUJIFILM Business Innovation Corp.

For more information, please visit www.fieri.com

Nothing herein should be construed as a warranty in addition to the express warranty statement provided with Fiery, LLC products and services.

ColorGuard, ColorRight, Command WorkStation, ColorWise, Fiery, the Fiery logo, Fiery Compose, Fiery Driven, the Fiery Driven logo, Fiery Edge, Fiery Essential, Fiery HyperRIP, Fiery Impose, Fiery Impress, Fiery ImageViewer, Fiery Intensify, Fiery JobExpert, Fiery JobFlow, Fiery JobMaster, Fiery Prep-it, Fiery Prints, the Fiery Prints logo, Fiery TrueBrand, FreeForm, MicroPress, IQ, PrintMe, RIPChips, RIP-While-Print, Spot-On, Spot Pro, and WebTools are trademarks or registered trademarks of Fiery, LLC and/or its wholly owned subsidiaries in the U.S. and/or certain other countries. All other terms and product names may be trademarks or registered trademarks of their respective owners and are hereby acknowledged.

© 2026 FIERY, LLC. ALL RIGHTS RESERVED.

